

**Garant****Stainless straight edge in a case, Length: 50mm****Order data**

Order number	460095 50
GTIN	4045197718600
Item class	41H

**Description****Version:**

Hardened, ground, and precision lapped straight edge. Wedge shaped cross section tapering to a point for inspection even in corners, grooves, cut outs etc. With plastic insulated handle to protection against body heat.

Made of **stainless** steel. **Both bevels anti-glare matt finished.**

**Note:**

The straightness tolerance of the measuring edge refers to a displacement range of  $\pm 15^\circ$  to the symmetry plane.

**Technical description**

Straightness tolerance of the measuring edge	0.002 mm
Length	50 mm
Standard	DIN 874
Material	stainless steel
Surface chamfer	non-glare matt finish
Packaging	Wallet
Calibration	F6
Type of product	Straight edge

**Services**

DAkKS calibration	Straight edge maximum length 500 mm	026010 500
Calibration	Straight edge maximum length 200 mm	026000 200