

Garant**Swing doors set, Usable depth 1350 mm, suitable for racking height: 2000mm****Order data**

Order number	993321 2000
GTIN	4062406097929
Item class	91W

Description**Version:**

The swing doors are reinforced on the inside, lockable by slide handle **with cylinder locks**. Can easily be upgraded to other GARANT locking systems. The racking bays behind the swing doors can be fitted with pull-out shelves. The doors open 180° to allow the shelves to be extended freely.

Colour:

Frame RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Technical description

suitable for racking height	2000 mm
Electronic locking system can be retrofitted	yes
Height	2000 mm
Door fronts	Plain sheet metal swing door
Material thickness	1.5 mm
Door opening angle	180 degrees

Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	Usable depth 1350 mm
Width	1020 mm
Depth	80 mm
suitable for racking usable width	920 mm
Type of product	Swing door