

## Garant

**Swing doors set, Usable depth 950 mm, suitable for racking height: 2000mm**



### Order data

Order number	993331 2000
GTIN	4062406097943
Item class	91W

### Description

#### Version:

The swing doors are reinforced on the inside, lockable by slide handle **with cylinder locks**. Can easily be upgraded to other GARANT locking systems. The racking bays behind the swing doors can be fitted with pull-out shelves. The doors open 180° to allow the shelves to be extended freely.

#### Colour:

Frame RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

### Technical description

Electronic locking system can be retrofitted	yes
Door fronts	Plain sheet metal swing door
suitable for racking height	2000 mm
Height	2000 mm
Application range	Heavy-duty racking
Material thickness	1.5 mm

Door opening angle	180 degrees
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	Usable depth 950 mm
Width	1420 mm
Depth	80 mm
suitable for racking usable width	1320 mm
Type of product	Swing door