

Garant

Heavy-duty extension rack with 1 column stile with 100 % extension pull-out shelf, Usable depth 1350 mm, Height: 2000mm

**Order data**

Order number	993411 2000
GTIN	4062406097981
Item class	91W

Description**Version:**

Column stiles of C-profile 100 mm wide are fitted with **3 or 4 full extension pull-out shelves** (100 % extension). Insertion holes at 50 mm intervals. **With locking bar (anti-tilt protection), top shelf, and rear panel (4-piece).**

Colour:

Frame and rear wall RAL 7035 light grey, pull-out shelves RAL 7016 anthracite **powder-coated.**

Note:

- **For safety the rack base plates must be anchored to the floor with suitable fastenings.**
- **The racks can be enclosed with side panels No. 993260; 993270, swing door sets No. 993321; 993331 and electrically-operated roller shutters No. 993310 – 993316.**
- **The following floor loading results from the maximum loading of one basic rack + 1 extension rack: Point load 2500 kg, area pressure 10 kg/cm², floor loading per m² 3290 kg/m².**
- **Supplied for self-assembly, saving freight costs. Delivered unassembled.**

Technical description

Bay load (individual bay)	4000 kg
Top shelf	500 kg
Number of pull-out shelves 100 %	3
Pull-out shelf load capacity	1000 kg
Pull-out shelf usable height	35 mm
Height	2000 mm
Usable height	1890 mm
Material thickness	2 mm
Drawer/pull-out shelf load capacity	1000 kg
Cabinet housing internal load capacity	4000 kg
Drawer runner extension (partial/full extension)	100 %
Drawer runner extension	Anti-tilt lock
Height adjustment interval	50 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	Usable depth 1350 mm
Width	1020 mm
Depth	1370 mm
Usable width	920 mm
Usable depth	1350 mm
Pull-out shelf usable width	830 mm
Pull-out shelf usable depth	1200 mm
Placing a pallet into storage	Pallets lengthways insertion
Type of product	Heavy-duty racking