

Garant**Assembly trolley, fitted with GARANT open storage bins, Number of open storage bins: 70****Order data**

Order number	918595 70
GTIN	4062406098056
Item class	91P

Description**Version:**

Assembly trolley No.918590 size1300, fitted with GARANT open storage bins.

Frame and structure of rectangular steel hollow section with sheet metal base. Insertion slots in the front and back of the frame (at 50 mm intervals) for fitting size 1000 mm shelves, multi-function rails etc. **Threaded sockets** on the inside of the frame for fitting perforated panels. **4 castors** (2 with parking brakes, \varnothing 125 mm) with treadless polyurethane tyres, roller bearing hubs and a large push handle with Haptoprene® cover ensures safe handling. Equipped with 6 Multifix open storage bins No. 928230 size 1000/AA1 and 4 No. 928230 size 1000/AB1.

Colour:

RAL 7035 light grey **powder coated**.

Technical description

Width	1100 mm
Width without handle	1000 mm
Depth	700 mm

Suspension interval	50 mm
maximum load capacity	200 kg
Number of castors without parking brake	2
Material of wheels	Treadless polyurethane tyres
Usable height	970 mm
Number of castors with parking brake	2
Number of open storage bins	70
Weight	81 kg
Wheel Ø	125 mm
Height	1300 mm
Design version	Steel hollow section construction
Material thickness	1.5 mm
Height adjustment interval	50 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Materials supply trolley

Accessories

Multifix rail open storage bins Length mm / Type 1000/AB1	928230 1000/AB1
Multifix rail open storage bins Length mm / Type 1000/AA1	928230 1000/AA1
Push handle Colour BLUE	920135 BLUE
Swivel castor Type 2	920137 2
Swivel castor Type 1	920137 1
Push handle Colour BLACK	920135 BLACK
Multifix suitable for type 1000	928201 1000
Materials supply trolley Height 1300 mm	918590 1300
Open storage bin Type AB1	963301 AB1
Open storage bin Type AA1	963301 AA1

