

**Garant****Assembly trolley, fitted with GARANT open storage bins, Number of open storage bins: 84****Order data**

Order number	918595 84
GTIN	4062406098063
Item class	91P

**Description****Version:**

Assembly trolley No.918590 size1300, fitted with GARANT open storage bins.

**Frame and structure** of rectangular steel hollow section with sheet metal base. Insertion slots in the front and back of the frame (at 50 mm intervals) for fitting size 1000 mm shelves, multi-function rails etc. **Threaded sockets** on the inside of the frame for fitting perforated panels. **4 castors** (2 with parking brakes,  $\varnothing$  125 mm) with treadless polyurethane tyres, roller bearing hubs and a large push handle with Haptoprene® cover ensures safe handling. Equipped with 6 Multifix open storage bins No. 928230 size 1000/AA1 and 6 No. 928230 size 1000/AB1.

**Colour:**

RAL 7035 light grey **powder coated**.

**Technical description**

Material of wheels	Treadless polyurethane tyres
Number of open storage bins	84
Weight	90 kg

maximum load capacity	200 kg
Suspension interval	50 mm
Number of castors with parking brake	2
Height	1300 mm
Usable height	970 mm
Width without handle	1000 mm
Number of castors without parking brake	2
Depth	700 mm
Wheel Ø	125 mm
Width	1100 mm
Design version	Steel hollow section construction
Material thickness	1.5 mm
Height adjustment interval	50 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Materials supply trolley

## Accessories

Push handle Colour BLUE	920135 BLUE
Swivel castor Type 2	920137 2
Multifix rail open storage bins Length mm / Type 1000/AB1	928230 1000/AB1
Swivel castor Type 1	920137 1
Multifix rail open storage bins Length mm / Type 1000/AA1	928230 1000/AA1
Push handle Colour BLACK	920135 BLACK
Materials supply trolley Height 1300 mm	918590 1300
Multifix suitable for type 1000	928201 1000
Open storage bin Type AB1	963301 AB1
Open storage bin Type AA1	963301 AA1

