



## High-performance cutting oil free of mineral oil UV 80, Contents: 0,25l



### Order data

|              |               |
|--------------|---------------|
| Order number | 084205 0,25   |
| GTIN         | 2050001770301 |
| Item class   | 08J           |

### Description

#### Version:

Cutting oil for the most demanding applications, can be washed off with water, viscosity adjustable for the application by adding water.

Application by brush, spray can, spray bottle or lubrication system.

#### Application:

Multi-purpose for **all machining operations** (turning, milling, drilling, tapping, reaming, broaching and sawing) and also for **forming**. Indispensable when cutting **difficult materials** such as stainless and heat-resistant steels, nickel alloys, titanium, and similar alloys. Ideal for **non-ferrous metals**.

**Ideal when minimum lubrication is required**, due to being free of mineral oil.

### Technical description

|                                  |                       |
|----------------------------------|-----------------------|
| Spontaneous ignition temperature | 325 °C                |
| Version                          | Spray bottle          |
| Colour                           | yellowish             |
| Kinematic viscosity              | 57 mm <sup>2</sup> /s |

|                     |                            |
|---------------------|----------------------------|
| Flashpoint          | > 180 °C                   |
| Storage temperature | 5 - 40 °C                  |
| Shape               | liquid                     |
| Contents            | 0.25 l                     |
| Type of product     | Cutting oil / grinding oil |