

SWISS TOOLS

Lever-lock toolholder right-hand, HSK-T, Shank Ø / insert size: 63/15HPmm**Order data**

Order number	320035 63/15HP
GTIN	2050001772527
Item class	36D

Description**Note:**

PSC clamping stud on request.

Order the suitable **HP nozzle** No. 320001 separately. Spare parts No.320610 – 320626 can be found in the spare parts list.

Technical description

Insert size	15
Spare part	P05
Overhang dimension A	70 mm
Axis tip distance f	45 mm
suitable indexable insert	DN.. 1506..
Minimum pre-drill Ø D ₁ min	80 mm
Shank Ø	63 mm
Adapter	HSK-T
Application type	right-hand
Arbor standard	ISO 12164-3

Through-coolant	yes
Shank type	Hollow shank taper
Type of product	Boring bar

Accessories

Clamping screw No. 3 Type P01	320611 P01
Clamping screw No. 3 Type P05	320611 P05
Toggle lever No. 4 Type P05	320612 P05
Tube pin No. 7 Type P06	320618 P06
Intermediate spacer No. 1 Type P01	320610 P01
Tube pin No. 7 Type P05	320618 P05
Intermediate spacer No. 1 Type P04	320610 P04
Nozzle ring No. 5 Type D07	320613 D07
Toggle lever No. 4 Type P04	320612 P04
High-pressure cooling nozzle (HP) Type 63	320001 63
Intermediate spacer No. 1 Type P05	320610 P05
Clamping screw No. 3 Type D07	320611 D07
Intermediate spacer No. 1 Type P02	320610 P02
Toggle lever No. 4 Type P02	320612 P02
Clamp No. 6 Type D07	320614 D07
Tube pin No. 7 Type P01	320618 P01
Intermediate spacer No. 1 Type P06	320610 P06
Clamping screw No. 3 Type P02	320611 P02
Tube pin No. 7 Type P02	320618 P02
Tube pin No. 7 Type P04	320618 P04
Toggle lever No. 4 Type P06	320612 P06
Toggle lever No. 4 Type P01	320612 P01
Clamping screw No. 3 Type P06	320611 P06

