

**Garant**
**Boring bar, steel, right-hand, Shank  $\varnothing$  / insert size: 1012/07mm**

**Order data**

Order number	260340 1012/07
GTIN	4062406099114
Item class	21T

**Technical description**

ISO code toolholder	A1012K SDQCR/L07
Minimum pre-drill $\varnothing D_{\min}$	15.5 mm
Head length $L_1$	27.5 mm
Neck width $L_4$	10.7 mm
Centre offset $L_3$	9 mm
Clamping height $L_2$	11 mm
Pack of insert screws	269028 7
suitable indexable insert	DC.. 0702..
Setting angle $\kappa$	107.5 degrees
Insert size	7 mm
Overall length $L$	125 mm
Usable depth $T$	4 mm
Shank $\varnothing D_s$	12 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring bar

---

## Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500