

Garant
Boring bar, steel, left-hand, Shank Ø / insert size: 1216/07mm

Order data

Order number	260341 1216/07
GTIN	4062406099152
Item class	21T

Technical description

Pack of insert screws	269028 7
Insert size	7 mm
Overall length L	150 mm
Centre offset L ₃	11 mm
ISO code toolholder	A1216M SDQCR/L07
Neck width L ₄	12 mm
suitable indexable insert	DC.. 0702..
Minimum pre-drill Ø D _{min}	19.5 mm
Clamping height L ₂	15 mm
Head length L ₁	39.5 mm
Setting angle κ	107.5 degrees
Usable depth T	5 mm
Shank Ø D _s	16 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500