

**Garant**
**Boring bar, steel, left-hand, Shank  $\varnothing$  / insert size: 1012/07mm**


## Order data

Order number	260341 1012/07
GTIN	4062406099145
Item class	21T

## Technical description

Overall length L	125 mm
Setting angle $\kappa$	107.5 degrees
Insert size	7 mm
Pack of insert screws	269028 7
Centre offset $L_3$	9 mm
Clamping height $L_2$	11 mm
ISO code toolholder	A1012K SDQCR/L07
suitable indexable insert	DC.. 0702..
Neck width $L_4$	10.7 mm
Minimum pre-drill $\varnothing D_{\min}$	15.5 mm
Head length $L_1$	27.5 mm
Usable depth T	4 mm
Shank $\varnothing D_s$	12 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3xD
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring bar

---

## Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500