

SWISS TOOLS

Lever-lock toolholder left-hand, HSK-T, Shank Ø / insert size: 63/12HPmm



Order data

Order number	320016 63/12HP
GTIN	2050001772978
Item class	36D

Description

Note:

Order the suitable **HP nozzle** No. 320001 separately. Spare parts No.320610 – 320626 can be found in the spare parts list.

PSC clamping stud on request.

Technical description

Insert size	12
suitable indexable insert	CN.. 1204..
Spare part	P01
Overhang dimension A	70 mm
Minimum pre-drill Ø D ₁ min	80 mm
Axis tip distance f	45 mm
Shank Ø	63 mm
Adapter	HSK-T
Application type	left-hand
Arbor standard	ISO 12164-3

Through-coolant	yes
Shank type	Hollow shank taper
Type of product	Boring bar

Accessories

Tube pin No. 7 Type P05	320618 P05
Intermediate spacer No. 1 Type P04	320610 P04
Intermediate spacer No. 1 Type P02	320610 P02
Nozzle ring No. 5 Type D07	320613 D07
Intermediate spacer No. 1 Type P06	320610 P06
Clamp No. 6 Type D07	320614 D07
Clamping screw No. 3 Type P01	320611 P01
Tube pin No. 7 Type P02	320618 P02
Toggle lever No. 4 Type P02	320612 P02
Clamping screw No. 3 Type P05	320611 P05
Clamping screw No. 3 Type P02	320611 P02
Toggle lever No. 4 Type P04	320612 P04
Toggle lever No. 4 Type P06	320612 P06
High-pressure cooling nozzle (HP) Type 63	320001 63
Tube pin No. 7 Type P01	320618 P01
Intermediate spacer No. 1 Type P01	320610 P01
Intermediate spacer No. 1 Type P05	320610 P05
Clamping screw No. 3 Type D07	320611 D07
Toggle lever No. 4 Type P05	320612 P05
Toggle lever No. 4 Type P01	320612 P01
Tube pin No. 7 Type P04	320618 P04
Clamping screw No. 3 Type P06	320611 P06
Tube pin No. 7 Type P06	320618 P06

