

SWISS TOOLS

## Lever-lock toolholder right-hand, PSC, Shank Ø / insert size: 63/08HPmm



### Order data

Order number	320305 63/08HP
GTIN	2050001772947
Item class	36D

### Description

#### Note:

Order the suitable **HP nozzle** No. 320001 separately. Spare parts No.320610 – 320626 can be found in the spare parts list.

PSC clamping stud on request.

### Technical description

suitable indexable insert	WN.. 0804..
Axis tip distance f	45 mm
Spare part	P04
Insert size	08
Minimum pre-drill Ø D <sub>1</sub> min	80 mm
Overhang dimension A	65 mm
Shank Ø	63 mm
Adapter	PSC
Application type	right-hand
Arbor standard	ISO 26623-1

Through-coolant	yes
Type of product	Boring bar

## Accessories

Clamp No. 6 Type D07	320614 D07
High-pressure cooling nozzle (HP) Type 63	320001 63
Clamping screw No. 3 Type P05	320611 P05
Clamping screw No. 3 Type P06	320611 P06
Intermediate spacer No. 1 Type P05	320610 P05
Toggle lever No. 4 Type P04	320612 P04
Toggle lever No. 4 Type P01	320612 P01
Intermediate spacer No. 1 Type P06	320610 P06
Tube pin No. 7 Type P06	320618 P06
Toggle lever No. 4 Type P05	320612 P05
Intermediate spacer No. 1 Type P02	320610 P02
Intermediate spacer No. 1 Type P01	320610 P01
Tube pin No. 7 Type P01	320618 P01
Clamping screw No. 3 Type P02	320611 P02
Clamping screw No. 3 Type D07	320611 D07
Toggle lever No. 4 Type P06	320612 P06
Clamping screw No. 3 Type P01	320611 P01
Tube pin No. 7 Type P04	320618 P04
Nozzle ring No. 5 Type D07	320613 D07
Tube pin No. 7 Type P02	320618 P02
Intermediate spacer No. 1 Type P04	320610 P04
Tube pin No. 7 Type P05	320618 P05
Toggle lever No. 4 Type P02	320612 P02