

SONO  SWISS®**PRESET ultrasonic cleaning unit, Capacity: 1l****Order data**

Order number	082923 1
GTIN	2050001962904
Item class	04E

Description**Version:**

Units of drawn or welded stainless steel. Temperature control from 30 °C to 80 °C in 5 °C steps. Stand-alone units: PRESET – drawn stainless steel for storing frequent applications.

Application:

For removal of oil, grease, grinding fluids, polishing fluids, paint residues, flux, oxide layers, carbon deposits, scale from nearly all surfaces and even from inaccessible places, whilst treating the component being cleaned with the utmost care. Use special power cleaners depending on the dirt and effectiveness required (from No. 082930). The component to be cleaned must be completely surrounded by cleaning fluid.

Supplied with:

Ultrasonic cleaning unit with cover, without basket (No. 082926).

Note:

Further sizes and types on request.

Component basket can be found under No. 082926 in the online shop.

Technical description

Maximum ultrasonic power	240 W
Cleaning bath height	60 mm
Extension option oil separator	no
Item length	206 mm

Capacity of cleaning bath	1 l
Item height	178 mm
Extension option rinsing module	no
Heating power	60 W
Cleaning bath width	85 mm
Item width	118 mm
Extension option pump filtration	no
Cleaning bath length	190 mm
Extension option drying module	no
Weight	2 kg
Width of component basket	66 mm
Nominal voltage	230 V
Power supply	Mains-powered
Power consumption	90 W
Length of component basket	172 mm
Nominal contents	0.8 l
Type of product	Ultrasonic cleaning unit

Accessories

Ultrasonic power cleanerT5 Capacity l/kg 10	082935 10
Ultrasonic power cleanerT1 Capacity l/kg 10	082930 10
Ultrasonic power cleanerT1 Capacity l/kg 2,5	082930 2,5
Component basket INOX Size suitable for No. 082922 / 082923 / 082924 1	082926 1
Ultrasonic power cleanerT4 Capacity l/kg 2,5	082934 2,5
Corrosion protection Capacity l/kg AK	082931 AK
Ultrasonic power cleanerT2 Capacity l/kg 10	082932 10
Ultrasonic power cleanerT2 Capacity l/kg 2,5	082932 2,5

Corrosion protection Capacity l/kg 1	082931 1
Ultrasonic power cleanerT4 Capacity l/kg 10	082934 10