

SONO  SWISS[®]**PRESET ultrasonic cleaning bath, Capacity: 12l****Order data**

Order number	082923 12
GTIN	2050001962713
Item class	04E

Description**Version:**

Made of drawn or welded stainless steel. Temperature control from 30 °C to 80 °C in 5 °C steps. Stand-alone units: PRESET – drawn stainless steel for storing frequent applications.

Application:

For removal of oil, grease, grinding fluids, polishing fluids, paint residues, flux, oxide layers, carbon deposits, scale from nearly all surfaces and even from inaccessible places, whilst treating the component being cleaned with the utmost care. Use special power cleaners depending on the dirt and effectiveness required (from No. 082930). The component to be cleaned must be completely surrounded by cleaning fluid.

Supplied with:

Ultrasonic cleaning unit with cover, without basket (No. 082926).

Note:

Further sizes and types on request.

Component basket can be found under No. 082926 in the online shop.

Technical description

Cleaning bath length	297 mm
Extension option oil separator	no
Item length	355 mm
Extension option drying module	no

Data sheet

Extension option rinsing module	no
Capacity of cleaning bath	12 l
Extension option pump filtration	no
Cleaning bath width	238 mm
Cleaning bath height	200 mm
Item width	290 mm
Heating power	800 W
Item height	320 mm
Weight	7.3 kg
Maximum ultrasonic power	800 W
Power supply	Mains-powered
Power consumption	1000 W
Width of component basket	181 mm
Nominal voltage	230 V
Length of component basket	240 mm
Nominal contents	9 l
Type of product	Ultrasonic cleaning unit

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/082923-12>