

SONO  SWISS®**PRESET ultrasonic cleaning unit, Capacity: 3l****Order data**

Order number	082923 3
GTIN	2050001962911
Item class	04E

Description**Version:**

Units of drawn or welded stainless steel. Temperature control from 30 °C to 80 °C in 5 °C steps. Stand-alone units: PRESET – drawn stainless steel for storing frequent applications.

Application:

For removal of oil, grease, grinding fluids, polishing fluids, paint residues, flux, oxide layers, carbon deposits, scale from nearly all surfaces and even from inaccessible places, whilst treating the component being cleaned with the utmost care. Use special power cleaners depending on the dirt and effectiveness required (from No. 082930). The component to be cleaned must be completely surrounded by cleaning fluid.

Supplied with:

Ultrasonic cleaning unit with cover, without basket (No. 082926).

Note:

Further sizes and types on request.

Component basket can be found under No. 082926 in the online shop.

Technical description

Item width	190 mm
Item height	220 mm
Cleaning bath height	97 mm
Item length	300 mm

Heating power	200 W
Extension option oil separator	no
Extension option drying module	no
Cleaning bath length	235 mm
Maximum ultrasonic power	320 W
Extension option rinsing module	no
Cleaning bath width	134 mm
Capacity of cleaning bath	3 l
Extension option pump filtration	no
Weight	2.8 kg
Length of component basket	191 mm
Power consumption	280 W
Power supply	Mains-powered
Width of component basket	95 mm
Nominal voltage	230 V
Nominal contents	1.9 l
Type of product	Ultrasonic cleaning unit

Accessories

Ultrasonic power cleanerT2 Capacity l/kg 10	082932 10
Ultrasonic power cleanerT4 Capacity l/kg 2,5	082934 2,5
Ultrasonic power cleanerT1 Capacity l/kg 10	082930 10
Corrosion protection Capacity l/kg AK	082931 AK
Component basket INOX Size suitable for No. 082922 / 082923 / 082924 3	082926 3
Corrosion protection Capacity l/kg 1	082931 1
Ultrasonic power cleanerT2 Capacity l/kg 2,5	082932 2,5
Ultrasonic power cleanerT1 Capacity l/kg 2,5	082930 2,5

Ultrasonic power cleanerT4 Capacity l/kg 10	082934 10
Ultrasonic power cleanerT5 Capacity l/kg 10	082935 10