

SONO  SWISS®**PRESET ultrasonic cleaning unit, Capacity: 30l****Order data**

Order number	082923 30
GTIN	2050001962720
Item class	04E

**Description****Version:**

Units of drawn or welded stainless steel. Temperature control from 30 °C to 80 °C in 5 °C steps. Stand-alone units: PRESET – drawn stainless steel for storing frequent applications.

**Application:**

For removal of oil, grease, grinding fluids, polishing fluids, paint residues, flux, oxide layers, carbon deposits, scale from nearly all surfaces and even from inaccessible places, whilst treating the component being cleaned with the utmost care. Use special power cleaners depending on the dirt and effectiveness required (from No. 082930). The component to be cleaned must be completely surrounded by cleaning fluid.

**Supplied with:**

Ultrasonic cleaning unit with cover, without basket (No. 082926).

**Note:**

Further sizes and types on request.

Component basket can be found under No. 082926 in the online shop.

**Technical description**

Maximum ultrasonic power	1200 W
Capacity of cleaning bath	30 l
Cleaning bath length	570 mm
Extension option pump filtration	no

Weight	11.2 kg
Extension option oil separator	no
Extension option drying module	no
Item width	355 mm
Heating power	1200 W
Cleaning bath width	330 mm
Extension option rinsing module	no
Item length	570 mm
Item height	320 mm
Cleaning bath height	200 mm
Nominal voltage	230 V
Width of component basket	238 mm
Power consumption	1500 W
Length of component basket	443 mm
Power supply	Mains-powered
Nominal contents	20.6 l
Type of product	Ultrasonic cleaning unit

## Accessories

Ultrasonic power cleanerT1 Capacity l/kg 2,5	082930 2,5
Ultrasonic power cleanerT4 Capacity l/kg 2,5	082934 2,5
Ultrasonic power cleanerT1 Capacity l/kg 10	082930 10
Ultrasonic power cleanerT2 Capacity l/kg 10	082932 10
Ultrasonic power cleanerT5 Capacity l/kg 10	082935 10
Ultrasonic power cleanerT4 Capacity l/kg 10	082934 10
Ultrasonic power cleanerT2 Capacity l/kg 2,5	082932 2,5
Component basket INOX Size suitable for No. 082922 / 082923 / 082924 30	082926 30

Corrosion protection Capacity l/kg AK	082931 AK
Corrosion protection Capacity l/kg 1	082931 1