

SONO  SWISS<sup>®</sup>**DURA-T ultrasonic cleaning bath, Capacity: 45l****Order data**

Order number	082924 45
GTIN	
Item class	04E

**Description****Version:**

Baths of drawn or welded stainless steel. Temperature control from 30 °C to 80 °C in 5 °C steps. Bench-top device: DURA-T – welded DUPLEX stainless steel baths suitable for multi-shift operation.

**Application:**

For removal of oil, grease, grinding fluids, polishing fluids, paint residues, flux, oxide layers, carbon deposits, scale from nearly all surfaces and even from inaccessible places, whilst treating the component being cleaned with the utmost care. Use special power cleaners depending on the dirt and effectiveness required (from No. 082930). The component to be cleaned must be completely surrounded by cleaning fluid.

**Supplied with:**

Ultrasonic cleaning bath with cover, without basket (No. 082926).

**Note:**

Further sizes and types on request.

Component basket can be found under No. 082926 in the online shop.

Item length: 600 mm

Item width: 425 mm

Item height: 467 mm

Length of component basket: 455 mm

Width of component basket: 265 mm

Cleaning bath height: 300 mm

## Technical description

Item length	600 mm
Cleaning bath length	500 mm
Heating power	1600 W
Item height	467 mm
Extension option oil separator	no
Weight	25.5 kg
Maximum ultrasonic power	1600 W
Cleaning bath width	300 mm
Extension option rinsing module	no
Capacity of cleaning bath	45 l
Cleaning bath height	300 mm
Extension option drying module	no
Item width	425 mm
Extension option pump filtration	no
Width of component basket	265 mm
Power supply	Mains-powered
Power consumption	2000 W
Length of component basket	455 mm
Nominal voltage	230 V
Nominal contents	35 l
Type of product	Ultrasonic cleaning unit

## Accessories

Ultrasonic power cleaner T4 Capacity l/kg 10	082934 10
Ultrasonic power cleaner T2 Capacity l/kg 10	082932 10
Ultrasonic power cleaner T3 Capacity l/kg 0,85	082933 0,85

Ultrasonic power cleaner T6 Capacity l/kg 10	082936 10
Ultrasonic power cleaner T1 Capacity l/kg T4	082930 T4
Ultrasonic power cleaner T2 Capacity l/kg 2,5	082932 2,5
Ultrasonic power cleaner T8 Capacity l/kg 2,5	082938 2,5
Ultrasonic power cleaner T1 Capacity l/kg 10	082930 10
Ultrasonic power cleaner T1 Capacity l/kg 2,5	082930 2,5
Ultrasonic power cleaner T1 Capacity l/kg T1	082930 T1
Ultrasonic power cleaner T1 Capacity l/kg T2	082930 T2
Ultrasonic power cleaner T3 Capacity l/kg 25	082933 25
Ultrasonic power cleaner T7 Capacity l/kg 2,5	082937 2,5
Corrosion protection Capacity l/kg AK	082931 AK
Ultrasonic power cleaner T8 Capacity l/kg 10	082938 10
Ultrasonic power cleaner T5 Capacity l/kg 2,5	082935 2,5
Ultrasonic power cleaner T5 Capacity l/kg 10	082935 10
Ultrasonic power cleaner T4 Capacity l/kg 2,5	082934 2,5
Component basket INOX Size suitable for No. 082922 / 082923 / 082924 45	082926 45
Cover Size suitable for No. 082922 / 082923 / 082924 45	082927 45
Ultrasonic power cleaner T6 Capacity l/kg 2,5	082936 2,5
Ultrasonic power cleaner T9 Capacity l/kg 10	082939 10
Corrosion protection Capacity l/kg 25	082931 25
Corrosion protection Capacity l/kg 1	082931 1
Ultrasonic power cleaner T1 Capacity l/kg T6	082930 T6
Ultrasonic power cleaner T7 Capacity l/kg 10	082937 10
Ultrasonic power cleaner T1 Capacity l/kg T5	082930 T5
Ultrasonic power cleaner T9 Capacity l/kg 2,5	082939 2,5
Ultrasonic power cleaner T1 Capacity l/kg T3	082930 T3