

**Machinable jaws, L × B1: 100X50mm****Order data**

Order number	370089 100X50
GTIN	2050001962126
Item class	37K

Description**Version:**

- **2 workpieces can be clamped.**
- **Maximum clamping stroke 0.5 mm.**

Material:

Clamping wedges of heat treatable steel.

Supplied with:

Including clamping for machining.

Technical description

Width B	72 mm
Height H	63 mm
Clamping force	5.5 kN
Ø D ₂	11.4 mm
maximum torque	46 Nm
Maximum machining depth T	15 mm
Type of product	Wedge clamp

