

**Clamping hook ground M12, Type: 7****Order data**

Order number	370073 7
GTIN	2050001962003
Item class	37K

Description**Application:**

For space-saving clamping of workpieces.
For higher clamping forces and greater stability.

Technical description

maximum torque	58.8 Nm
Type	7
Height H_2	27 mm
H_1	39 mm
Length 1	40 mm
$F_{max.}$	22.6 kN
$\varnothing D_{h7}$	25 mm
Type of product	Clamping hook

