



Machinable jaws, L × B1: 80X32mm



Order data

Order number	370089 80X32
GTIN	2050001962102
Item class	37K

Description

Version:

- 2 workpieces can be clamped.
- Maximum clamping stroke 0.5 mm.

Material:

Clamping wedges of heat treatable steel.

Supplied with:

Including clamping for machining.

Technical description

Height H	42 mm
Clamping force	2.5 kN
Width B	50 mm
Ø D ₂	7.7 mm
maximum torque	14 Nm
Maximum machining depth T	10 mm
Type of product	Wedge clamp

