



Clamping hook ground M12, Type: 8



Order data

Order number	370073 8
GTIN	2050001962010
Item class	37K

Description

Application:

For space-saving clamping of workpieces.
For higher clamping forces and greater stability.

Technical description

maximum torque	49 Nm
Length 1	50 mm
Height H ₂	29 mm
Type	8
H ₁	39 mm
F _{max.}	18.5 kN
Ø D _{h7}	25 mm
Type of product	Clamping hook

