

**Machinable jaws, L × B1: 40X32mm****Order data**

Order number	370089 40X32
GTIN	2050001962096
Item class	37K

Description**Version:**

- **2 workpieces can be clamped.**
- **Maximum clamping stroke 0.5 mm.**

Material:

Clamping wedges of heat treatable steel.

Supplied with:

Including clamping for machining.

Technical description

Clamping force	2.5 kN
Width B	50 mm
Height H	42 mm
Ø D ₂	7.4 mm
maximum torque	7.5 Nm
Maximum machining depth T	10 mm
Type of product	Wedge clamp

