

SONO  SWISS[®]**DURA-S ultrasonic cleaning bath, Capacity: 220l****Order data**

Order number	082925 220
GTIN	
Item class	04E

Description**Version:**

Baths of drawn or welded stainless steel. Temperature control from 30 °C to 80 °C in 5 °C steps. Free-standing device: DURA-S– Multi-frequency device made from duplex stainless steel, short circuit-proof generator with power regulator

Application:

For removal of oil, grease, grinding fluids, polishing fluids, paint residues, flux, oxide layers, carbon deposits, scale from nearly all surfaces and even from inaccessible places, whilst treating the component being cleaned with the utmost care. Use special power cleaners depending on the dirt and effectiveness required (from No. 082930). The component to be cleaned must be completely surrounded by cleaning fluid.

Supplied with:

Ultrasonic cleaning bath with cover, without basket (No. 082926).

Note:

Further sizes and types on request.

Component basket can be found under No. 082926 in the online shop.

Item length: 800 mm

Item width: 900 mm

Item height: 800 mm

Length of component basket: 630 mm

Width of component basket: 600 mm

Cleaning bath height: 550 mm

Technical description

Weight	110 kg
Extension option oil separator	no
Maximum ultrasonic power	3600 W
Extension option drying module	no
Item width	900 mm
Cleaning bath width	650 mm
Cleaning bath height	550 mm
Heating power	10000 W
Capacity of cleaning bath	220 l
Extension option rinsing module	no
Cleaning bath length	750 mm
Item height	800 mm
Item length	800 mm
Extension option pump filtration	no
Length of component basket	630 mm
Power consumption	11940 W
Width of component basket	600 mm
Power supply	Mains-powered
Nominal voltage	400 V
Nominal contents	220 l
Type of product	Ultrasonic cleaning unit

Accessories

Ultrasonic power cleaner T8 Capacity l/kg 2,5	082938 2,5
Ultrasonic power cleaner T7 Capacity l/kg 2,5	082937 2,5

Ultrasonic power cleaner T1 Capacity l/kg T1	082930 T1
Ultrasonic power cleaner T6 Capacity l/kg 2,5	082936 2,5
Ultrasonic power cleaner T1 Capacity l/kg T3	082930 T3
Ultrasonic power cleaner T9 Capacity l/kg 2,5	082939 2,5
Ultrasonic power cleaner T3 Capacity l/kg 25	082933 25
Ultrasonic power cleaner T1 Capacity l/kg T6	082930 T6
Ultrasonic power cleaner T1 Capacity l/kg T4	082930 T4
Ultrasonic power cleaner T3 Capacity l/kg 0,85	082933 0,85
Ultrasonic power cleaner T2 Capacity l/kg 10	082932 10
Ultrasonic power cleaner T4 Capacity l/kg 2,5	082934 2,5
Corrosion protection Capacity l/kg AK	082931 AK
Ultrasonic power cleaner T9 Capacity l/kg 10	082939 10
Ultrasonic power cleaner T5 Capacity l/kg 2,5	082935 2,5
Ultrasonic power cleaner T8 Capacity l/kg 10	082938 10
Corrosion protection Capacity l/kg 25	082931 25
Ultrasonic power cleaner T1 Capacity l/kg 2,5	082930 2,5
Ultrasonic power cleaner T1 Capacity l/kg 10	082930 10
Ultrasonic power cleaner T6 Capacity l/kg 10	082936 10
Ultrasonic power cleaner T5 Capacity l/kg 10	082935 10
Ultrasonic power cleaner T2 Capacity l/kg 2,5	082932 2,5
Ultrasonic power cleaner T4 Capacity l/kg 10	082934 10
Ultrasonic power cleaner T7 Capacity l/kg 10	082937 10
Ultrasonic power cleaner T1 Capacity l/kg T2	082930 T2
Component basket INOX Size suitable for No. 082922 / 082923 / 082924 220	082926 220
Corrosion protection Capacity l/kg 1	082931 1
Ultrasonic power cleaner T1 Capacity l/kg T5	082930 T5