

**Cutting head, left-hand, System / insert size: QC/11S****Order data**

Order number	260917 QC/11S
GTIN	4251414902787
Item class	29D

**Description****Version:**

Interchangeable cutting heads for **vibration-damping base bodies**. Narrow version.

**Application:**

Vibration damping effect up a maximum overhang of **14×D**.

Through-coolant: yes

System: QC

ISO code indexable cutting head: STUCR/L 11

suitable indexable insert: TC.. 1102..

suitable base body: 264900 – 264908

Minimum pre-drill Ø D<sub>min</sub>: 22 mm

Centre-line offset: 11 mm

Overall length: 20 mm

**Technical description**

Shank Ø	20 mm
Insert size	11 mm
ISO code indexable cutting head	STUCR/L 11

suitable base body	264900 – 264908
suitable indexable insert	TC.. 1102..
Centre-line offset	11 mm
System	QC
Overall length	20 mm
Minimum pre-drill Ø D <sub>min</sub>	22 mm
Series	Cutting head
Insert screw	269022 4
Application type	left-hand
Through-coolant	yes
Setting angle κ	93 degrees
Application	Internal longitudinal turning

## Accessories

Clamping screw	269407
Torx® bit, shank E 6.3 Torx® profile TX8	674248 TX8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cN·m	659906 500