

Garant
Boring bar carbide, left-hand, Shank \varnothing / insert size: 20/11 mm

Order data

Order number	261119 20/11
GTIN	4062406099848
Item class	21T

Technical description

Clamping height L_2	18 mm
Head length L_1	20.5 mm
Overall length L	250 mm
ISO code toolholder	E20S SVUBR/L 11
Centre offset L_3	13 mm
Minimum pre-drill $\varnothing D_{\min}$	25 mm
suitable indexable insert	VB.. 1103..
Insert size	11 mm
Pack of insert screws	269028 7
Setting angle κ	93 degrees
Shank $\varnothing D_s$	20 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	8xD
Tool material	Carbide
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar