

**Garant**
**Boring bar carbide, right-hand, Shank  $\varnothing$  / insert size: 20/11 mm**

**Order data**

Order number	261118 20/11
GTIN	4062406099817
Item class	21T

**Technical description**

ISO code toolholder	E20S SVUBR/L 11
Setting angle $\kappa$	93 degrees
Overall length L	250 mm
Clamping height $L_2$	18 mm
Insert size	11 mm
suitable indexable insert	VB.. 1103..
Pack of insert screws	269028 7
Centre offset $L_3$	13 mm
Minimum pre-drill $\varnothing D_{\min}$	25 mm
Head length $L_1$	20.5 mm
Shank $\varnothing D_s$	20 mm
Standard	DIN 8024
Application type	right-hand
Boring depth up to	8xD
Tool material	Carbide
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar