

Garant
Boring bar carbide, left-hand, Shank \varnothing / insert size: 25/11 mm

Order data

Order number	261119 25/11
GTIN	4062406099855
Item class	21T

Technical description

Pack of insert screws	269028 7
Clamping height L_2	23 mm
Centre offset L_3	17 mm
suitable indexable insert	VB.. 1103..
Minimum pre-drill $\varnothing D_{\min}$	31.5 mm
Insert size	11 mm
ISO code toolholder	E25S SVUBR/L 11
Head length L_1	23 mm
Setting angle κ	93 degrees
Overall length L	250 mm
Shank $\varnothing D_s$	25 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	8xD
Tool material	Carbide
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar