

**Garant**

**Side lock arbors Form ADB with cooling channel bore, BT 50 A = 100,  
Clamping range  $\varnothing$  D1: 8mm**


**Order data**

Order number	302655 8
GTIN	4062406100155
Item class	31A

**Description**
**Version:**

All shanks hard turned (for smooth running). Balancing quality G2.5 / 25,000 rpm. **With coolant supply holes that can be plugged.**

**Application:**

For clamping tools with side flats to DIN 1835 B and DIN 6535 HB.

**Optional extras:**

Pull studs (PS) No. 308760 – 308802. Pull stud wrenches No. 308820; 308835.

**Technical description**

External $\varnothing$ D	28 mm
Overhang dimension A	100 mm
Clamping $\varnothing$ D <sub>1</sub>	8 mm
Spare clamping screw No. 30 9900	8
Adapter	BT 50 A = 100
Standard	DIN 6359
Arbor standard	ISO 7388-2
Arbor standard	JIS B6339

Shape	ADB
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 μm
Machining strategy	HPC
Type of product	Side lock arbor

## Accessories

Pull stud 45°sealed suitable for steep tapers 50	308760 50
Pull stud 45°sealed suitable for steep tapers 50	308765 50
Pull stud 60°sealed suitable for steep tapers 50	308785 50
Pull stud 90°sealed suitable for steep tapers 50	308795 50
Wrench for pull studsISO 7388 suitable for ISO taper size 50	308830 50
Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 50	308820 50
Pull stud 90°sealed suitable for steep tapers 50	308790 50
Spare clamping screw for chucks with clamping Ø D1 8 mm	309900 8