

**Garant**
**Side lock arbor Form ADB with cooling channel bore, BT 40 A = 100, Clamping range  $\varnothing$  D1: 20mm**

**Order data**

Order number	302606 20
GTIN	4062406100131
Item class	31A

**Description**
**Version:**

All shanks hard turned (for smooth running). Balancing quality G2.5 / 25,000 rpm. **With coolant supply holes that can be plugged.**

**Application:**

For clamping tools with side flats to DIN 1835 B and DIN 6535 HB.

**Optional extras:**

Pull studs (PS) No. 308760 – 308802. Pull stud wrenches No. 308820; 308835.

**Technical description**

Overhang dimension A	100 mm
External $\varnothing$ D	52 mm
Clamping $\varnothing$ D <sub>1</sub>	20 mm
Spare clamping screw No. 30 9900	20
Adapter	BT 40 A = 100
Standard	DIN 6359
Arbor standard	ISO 7388-2
Arbor standard	JIS B6339
Shape	ADB

Concentricity	≤ 3 µm
Machining strategy	HPC
Type of product	Side lock arbor

## Accessories

Pull stud 45°sealed suitable for steep tapers 40	308760 40
Pull stud Hurco 90° with fitsealed suitable for steep tapers 40	308806 40
Pull stud 90°sealed suitable for steep tapers 40	308790 40
Pull stud Hurco 45° with fitsealed suitable for steep tapers 40	308802 40
Pull stud 90°sealed suitable for steep tapers 40	308795 40
Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 40	308820 40
Hurco 45° pull stud with 4-mm bore and fitsealed suitable for steep tapers 40	308801 40
Wrench for pull studsISO 7388 suitable for ISO taper size 40	308830 40
Pull stud 60°sealed suitable for steep tapers 40	308785 40
Pull stud 45°sealed suitable for steep tapers 40	308765 40
Spare clamping screw for chucks with clamping Ø D1 20 mm	309900 20