



Pneumatic die grinder, Type: SMP60



Order data

Order number	079440 SMP60
GTIN	5000630
Item class	03P

Description

Version:

ATA – Pneumatic straight grinders **with 3 mm collets** for fine milling, grinding and engraving.

Integral pre-filter. Turbine-driven small straight die grinder with a **maximum speed of 60,000 rpm.**

Technical description

Output power	85 W
Collet Ø	3 mm
Operating noise	68 dB(A)
Manufacturer's designation	SPM 60 R
Weight	0.17 kg
maximum air consumption	230 l/min
maximum speed	60000 min ⁻¹
maximum vibration to EN	< 2.5 m/s ²
Length	140 mm
Compressed air connection	1/4 in
Connection thread	BSP
Type of product	Straight die grinder

