



## Boring bar carbide, right-hand, Shank $\varnothing$ / insert size: 20/11 mm



### Order data

Order number	261326 20/11
GTIN	4062406100506
Item class	21T

### Description

Boring bar carbide 20/11 mm ISO code toolholder: E20S SVJCR/L11

Setting angle  $\kappa$ : 142 degrees

suitable indexable insert: VC..1103..

Minimum pre-drill  $\varnothing D_{\min}$ : 24 mm

Centre-line offset: 2 mm

Clamping height H: 19 mm

### Technical description

Overall length L	250 mm
Insert size	11 mm
Neck width	11 mm
suitable indexable insert	VC..1103..
Pack of insert screws	269028 7
Centre-line offset	2 mm
Clamping height H	19 mm
Head length	38 mm
Minimum pre-drill $\varnothing D_{\min}$	24 mm
ISO code toolholder	E20S SVJCR/L11
Setting angle $\kappa$	142 degrees
Shank $\varnothing$	20 mm
Application type	right-hand

Boring depth up to	8×D
Tool material	Carbide
Standard	DIN 8024
Through-coolant	yes
Shank type	Boring bar
Application	Internal longitudinal turning
Type of product	Boring bar