

**Garant**
**Boring bar carbide, right-hand, Shank  $\varnothing$  / insert size: 12/07mm**

**Order data**

Order number	261326 12/07
GTIN	4062406100452
Item class	21T

**Technical description**

ISO code toolholder	E12M SVJCR/L07
Centre offset $L_3$	2 mm
Overall length L	150 mm
Neck width $L_4$	7.8 mm
suitable indexable insert	VC.. 0702..
Pack of insert screws	269028 27
Insert size	7 mm
Head length $L_1$	18 mm
Setting angle $\kappa$	142 degrees
Clamping height $L_2$	11 mm
Minimum pre-drill $\varnothing D_{\min}$	13 mm
Shank $\varnothing D_s$	12 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	8xD
Tool material	Carbide
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring bar