

Garant
Boring bar carbide, left-hand, Shank \varnothing / insert size: 8/05mm

Order data

Order number	261327 8/05
GTIN	4062406100575
Item class	21T

Technical description

Insert size	5 mm
Neck width L_4	6 mm
ISO code toolholder	E08F SVJCR/L05
Centre offset L_3	3 mm
Pack of insert screws	269028 26
Clamping height L_2	7.5 mm
Minimum pre-drill $\varnothing D_{\min}$	8 mm
Overall length L	80 mm
Head length L_1	26 mm
Setting angle κ	142 degrees
suitable indexable insert	VC.. 0501..
Shank $\varnothing D_s$	8 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	8xD
Tool material	Carbide
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring bar