

Garant
Boring bar carbide, left-hand, Shank \varnothing / insert size: 16/11mm

Order data

Order number	261327 16/11
GTIN	4062406100650
Item class	21T

Technical description

Minimum pre-drill $\varnothing D_{\min}$	22 mm
suitable indexable insert	VC.. 1103..
Pack of insert screws	269028 27
Overall length L	200 mm
Centre offset L_3	2 mm
Insert size	11 mm
Setting angle κ	142 degrees
Head length L_1	31.4 mm
ISO code toolholder	E16R SVJCR/L11
Neck width L_4	9.5 mm
Clamping height L_2	15 mm
Shank $\varnothing D_s$	16 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	8xD
Tool material	Carbide
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring bar