

Garant
Boring bar carbide, left-hand, Shank \varnothing / insert size: 10/07mm

Order data

Order number	261327 10/07
GTIN	4062406100636
Item class	21T

Technical description

Neck width L_4	6.3 mm
Head length L_1	18 mm
Setting angle κ	142 degrees
Overall length L	125 mm
Minimum pre-drill $\varnothing D_{\min}$	13 mm
Insert size	7 mm
suitable indexable insert	VC.. 0702..
Pack of insert screws	269028 27
Centre offset L_3	1.5 mm
Clamping height L_2	9 mm
ISO code toolholder	E10K SVJCR/L07
Shank $\varnothing D_s$	10 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	8xD
Tool material	Carbide
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring bar