

Garant
Boring bar carbide, left-hand, Shank \varnothing / insert size: 12/07mm

Order data

Order number	261327 12/07
GTIN	4062406100643
Item class	21T

Technical description

Pack of insert screws	269028 27
suitable indexable insert	VC.. 0702..
Setting angle κ	142 degrees
Head length L_1	18 mm
Centre offset L_3	2 mm
Insert size	7 mm
Clamping height L_2	11 mm
Neck width L_4	7.8 mm
Minimum pre-drill $\varnothing D_{\min}$	13 mm
ISO code toolholder	E12M SVJCR/L07
Overall length L	150 mm
Shank $\varnothing D_s$	12 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	8xD
Tool material	Carbide
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring bar