



Side lock arbor Form AD, BT 40 short, Clamping range \varnothing D1: 10mm



Order data

Order number	302607 10
GTIN	4062406100742
Item class	32A

Description

Version:

All shanks fine bead blasted. Balancing quality G6.3 / 18,000 rpm.

Application:

For clamping tools with side flats to DIN 1835 B and DIN 6535 HB.

Optional extras:

Pull studs (PS) No. 308760 – 308802. Pull stud wrenches No. 308820; 308835.

Technical description

Clamping \varnothing D ₁	10 mm
External \varnothing D	35 mm
Overhang dimension A	63 mm
Spare clamping screw No. 30 9900	10
Adapter	BT 40 short
Standard	DIN 6359
Arbor standard	ISO 7388-2
Arbor standard	JIS B6339
Shape	AD
Balance quality G at rotational speed	G 6.3 at 18,000 rpm

Concentricity	≤ 3 µm
Machining strategy	HPC
Type of product	Side lock arbor

Accessories

Hurco 45° pull stud with 4-mm bore and fitsealed suitable for steep tapers 40	308801 40
Wrench for pull studs ISO 7388 suitable for ISO taper size 40	308830 40
Pull stud Hurco 45° with fitsealed suitable for steep tapers 40	308802 40
Pull stud 90° sealed suitable for steep tapers 40	308795 40
Wrench for pull studs DIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 40	308820 40
Pull stud 60° sealed suitable for steep tapers 40	308785 40
Pull stud 45° sealed suitable for steep tapers 40	308760 40
Pull stud 45° sealed suitable for steep tapers 40	308765 40
Pull stud Hurco 90° with fitsealed suitable for steep tapers 40	308806 40
Pull stud 90° sealed suitable for steep tapers 40	308790 40
Spare clamping screw for chucks with clamping Ø D1 10 mm	309900 10