

Garant
Boring bar carbide, right-hand, Shank \varnothing / insert size: 16/11 mm

Order data

Order number	261328 16/11
GTIN	4062406100698
Item class	21T

Technical description

Clamping height L_2	15 mm
Pack of insert screws	269028 7
Insert size	11 mm
suitable indexable insert	VC.. 1103..
Head length L_1	16.5 mm
Centre offset L_3	11 mm
Overall length L	200 mm
Minimum pre-drill $\varnothing D_{\min}$	21 mm
ISO code toolholder	E16R SVUCR/L11
Setting angle κ	93 degrees
Shank $\varnothing D_s$	16 mm
Standard	DIN 8024
Application type	right-hand
Boring depth up to	8xD
Tool material	Carbide
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar