

Garant
Boring bar carbide, right-hand, Shank \varnothing / insert size: 25/11 mm

Order data

Order number	261328 25/11
GTIN	4062406100810
Item class	21T

Technical description

Clamping height L_2	23 mm
suitable indexable insert	VC.. 1103..
Head length L_1	23 mm
Centre offset L_3	17 mm
Minimum pre-drill $\varnothing D_{\min}$	31.5 mm
Setting angle κ	93 degrees
ISO code toolholder	E25S SVUCR/L11
Pack of insert screws	269028 7
Insert size	11 mm
Overall length L	250 mm
Shank $\varnothing D_s$	25 mm
Standard	DIN 8024
Application type	right-hand
Boring depth up to	8xD
Tool material	Carbide
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar