

Garant
Boring bar carbide, left-hand, Shank \varnothing / insert size: 25/11 mm

Order data

| | |
|--------------|---------------|
| Order number | 261329 25/11 |
| GTIN | 4062406100841 |
| Item class | 21T |

Technical description

| | |
|--|-------------------------------|
| Head length L_1 | 23 mm |
| Setting angle κ | 93 degrees |
| Overall length L | 250 mm |
| suitable indexable insert | VC.. 1103.. |
| ISO code toolholder | E25S SVUCR/L11 |
| Insert size | 11 mm |
| Centre offset L_3 | 17 mm |
| Minimum pre-drill $\varnothing D_{\min}$ | 31.5 mm |
| Clamping height L_2 | 23 mm |
| Pack of insert screws | 269028 7 |
| Shank $\varnothing D_s$ | 25 mm |
| Standard | DIN 8024 |
| Application type | left-hand |
| Boring depth up to | 8xD |
| Tool material | Carbide |
| Through-coolant | yes |
| Application | Internal longitudinal turning |

Type of product

Boring bar