

Garant
Boring bar carbide, left-hand, Shank \varnothing / insert size: 16/11mm

Order data

Order number	261329 16/11
GTIN	4062406100827
Item class	21T

Technical description

Head length L_1	16.5 mm
Clamping height L_2	15 mm
Insert size	11 mm
Pack of insert screws	269028 7
Minimum pre-drill $\varnothing D_{\min}$	21 mm
suitable indexable insert	VC.. 1103..
Setting angle κ	93 degrees
Overall length L	200 mm
Centre offset L_3	11 mm
ISO code toolholder	E16R SVUCR/L11
Shank $\varnothing D_s$	16 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	8xD
Tool material	Carbide
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar