



Side lock arbor Form AD, BT 50 short, Clamping range \varnothing D1: 25mm



Order data

Order number	302657 25
GTIN	4062406100964
Item class	32A

Description

Version:

All shanks fine bead blasted. Balancing quality G6.3 / 18,000 rpm.

Application:

For clamping tools with side flats to DIN 1835 B and DIN 6535 HB.

Optional extras:

Pull studs (PS) No. 308760 – 308802. Pull stud wrenches No. 308820; 308835.

Technical description

Clamping \varnothing D ₁	25 mm
External \varnothing D	65 mm
Overhang dimension A	100 mm
Spare clamping screw No. 30 9900	25
Adapter	BT 50 short
Standard	DIN 6359
Arbor standard	ISO 7388-2
Arbor standard	JIS B6339
Balance quality G at rotational speed	G 6.3 at 18,000 rpm
Concentricity	$\leq 3 \mu\text{m}$

Machining strategy	HPC
Type of product	Side lock arbor

Accessories

Pull stud 45°sealed suitable for steep tapers 50	308760 50
Pull stud 90°sealed suitable for steep tapers 50	308790 50
Wrench for pull studsISO 7388 suitable for ISO taper size 50	308830 50
Pull stud 90°sealed suitable for steep tapers 50	308795 50
Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 50	308820 50
Pull stud 60°sealed suitable for steep tapers 50	308785 50
Pull stud 45°sealed suitable for steep tapers 50	308765 50
Spare clamping screw for chucks with clamping Ø D1 25 mm	309900 25