



ER collet chuck Form AD, BT 30 A = 60, for ER collet size: 20



Order data

Order number	302747 20
GTIN	4062406100995
Item class	32A

Description

Version:

External and internal taper ground.

- **All shanks fine bead blasted. Balancing quality G6.3 / 18,000 rpm.**
- **High-quality precision clamping nut.**

Application:

For clamping tools with parallel shank in collets to **DIN 6499 Form A and B.**

Supplied with:

ER clamping nut.

Optional extras:

ER collets No. 308881 – 309434, ER chuck keys No. 309680 – 309745 or No. 613300.

Pull studs (PS) No. 308760 – 308802. Pull stud wrenches No. 308820; 308835.

Note:

Matching clamping nut No. 309580 or 309610.

Machining strategy: HSC

Clamping range: 1 - 13 mm

Overhang dimension A: 60 mm

External Ø D: 34 mm

Spare ER clamping nut: 20

ER chuck key: 20

Technical description

Clamping range	1 - 13 mm
----------------	-----------

ER chuck key	20
Spare ER clamping nut	20
Overhang dimension A	60 mm
External \varnothing D	34 mm
Clamping \varnothing D ₁	1-13 mm
Adapter	BT 30 A = 60
Arbor standard	JIS B6339
Arbor standard	JIS B6339
Concentricity	$\leq 3 \mu\text{m}$
Machining strategy	HSC
Type of product	Collet chuck