



Digital caliper IP67, Measuring range: 300mm



Order data

Order number	412751 300
GTIN	4062406100889
Item class	42A

Description

Version:

Large high-contrast digital display. The measuring faces are precision-lapped. The caliper is resistant to water and dust. After 2 hours without movement, the control system shuts down the caliper automatically. Shock-resistant plastic casing.

Standard:

Clearly legible, high-contrast digital display. The calliper is resistant to water, coolant, oil, and dust. The measuring faces are precision lapped.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching. IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

Battery No. 081560 size CR2032.

Packaging: sturdy box

Standard: DIN 862

Reversible reading: mm / inch

Depth gauge: flat

IP Index of Protection: IP 67

Calibration: A1

Scale divisions: 0.01 mm

Scale divisions: 0.0005 in

Error limit: 0.04 mm

Jaw length: 40 mm

Technical description

Scale divisions	0.01 mm
Error limit	0.04 mm
Measuring range	0 - 300 mm
Depth gauge available	yes
Number of batteries contained	1
Jaw length	40 mm
Article no of the battery / rechargeable battery fitted	081560 CR2032
Auto switch-off	yes
Reversible reading	mm / inch
Scale divisions	0.0005 in
Calibration	A1
Depth gauge	flat
Material of the housing	Plastic
Standard	DIN 862
IP Index of Protection	IP 67
Power supply	Battery-powered
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Universal calipers

Services

Calibration Calipers / depth gauges maximum measuring range 300 mm	011030 300
DAkkS calibration Calipers / depth gauges maximum measuring range 300 mm	011050 300
Labelling laser-etched Type	018940
Calibration Calipers / depth gauges maximum measuring range 300 mm	021000 300

DAkkS calibration Calipers / depth gauges maximum
measuring range 300 mm

021010 300

Accessories

Button cell / special battery Battery type CR2032

081560 CR2032

Screw for depth gauge holder

412230