



## Digital caliper IP67, Measuring range: 200mm



### Order data

Order number	412751 200
GTIN	4062406100858
Item class	42A

### Description

#### Version:

Large high-contrast digital display. The measuring faces are precision-lapped. The caliper is resistant to water and dust. After 2 hours without movement, the control system shuts down the caliper automatically. Shock-resistant plastic casing.

#### Version of the advertising text:

Clearly legible, high-contrast digital display. The calliper is resistant to water, coolant, oil, and dust. The measuring faces are precision lapped.

#### Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

#### Supplied with:

Battery No. 081560 size CR2032.

### Technical description

Standard	ISO 13385
Scale divisions	0.0005 in
Measuring range	0 - 200 mm
Material of the housing	Plastic
Reversible reading	mm / inch
Depth gauge available	yes
Depth gauge	rectangular 3.7×1.3

Calibration	A1
Scale divisions	0.01 mm
Auto switch-off	yes
Jaw length	50 mm
Article no of the battery / rechargeable battery fitted	081560 CR2032
Number of batteries contained	1
IP Index of Protection	IP 67
Power supply	Battery-powered
Measurement deviation E MPE	±0.03 mm
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Universal calipers

## Services

CalibrationCalipers / depth gauges maximum measuring range 200 mm	021000 200
DAkkS calibrationCalipers / depth gauges maximum measuring range 200 mm	021010 200

## Accessories

Button cell / special battery Battery type CR2032	081560 CR2032
Screw for depth gauge holder	412230
Screw for depth gauge holder	412236