

**Digital caliper IP67 with rod type depth gauge, Measuring range: 150mm****Order data**

Order number	412749 150
GTIN	4062406101213
Item class	42A

Description**Version:**

Large high-contrast digital display. The measuring faces are precision-lapped. The caliper is resistant to water and dust. After 2 hours without movement, the control system shuts down the caliper automatically. Shock-resistant plastic casing.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

Including battery No. 081560 size CR2032.

Technical description

Material of the housing	Plastic
Scale divisions	0.0005 in
Depth gauge available	yes
Measuring range	0 - 150 mm
Article no of the battery / rechargeable battery fitted	081560 CR2032
Scale divisions	0.01 mm
Jaw length	40 mm
Reversible reading	mm / inch
Depth gauge	Ø 1.6

Calibration	A1
Standard	ISO 13385
Auto switch-off	yes
Number of batteries contained	1
IP Index of Protection	IP 67
Power supply	Battery-powered
Measurement deviation E MPE	± 0.03 mm
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Universal calipers

Services

DAkkS calibrationCalipers / depth gauges maximum measuring range 200 mm	021010 200
CalibrationCalipers / depth gauges maximum measuring range 200 mm	021000 200

Accessories

Button cell / special battery Battery type CR2032	081560 CR2032
Screw for depth gauge holder	412236