



Face mill arbor Form A, BT 50 A = 100, Spigot Ø d1: 27mm



Order data

| | |
|--------------|---------------|
| Order number | 303037 27 |
| GTIN | 4062406101268 |
| Item class | 32A |

Description

Version:

Taper shank, spigots, and contact surfaces ground on collar.
All shanks fine bead blasted. Balancing quality G6.3 / 18,000 rpm. Form A.

Supplied with:

Lock screw.

Optional extras:

Pull studs (PS) No. 308760 – 308802. Special toggle spanner No. 309840.

Technical description

| | |
|---|---------------|
| Spare milling cutter lock screw No. 309860 / 309861 | 27 |
| External Ø D | 60 mm |
| Spigot Ø d ₁ | 27 mm |
| Overhang dimension A | 100 mm |
| Suitable toggle spanner No. 309840 | 27 |
| Clamping Ø D ₁ | 27 mm |
| Adapter | BT 50 A = 100 |
| Standard | DIN 6357 |
| Arbor standard | JIS B6339 |

| | |
|---------------------------------------|----------------------|
| Arbor standard | ISO 7388-2 |
| Shape | A |
| Balance quality G at rotational speed | G 6.3 at 18,000 rpm |
| Concentricity | $\leq 5 \mu\text{m}$ |
| Machining strategy | HPC |
| Type of product | Milling head arbor |