



Digital caliper IP67, Measuring range: 150mm



Order data

Order number	412733 150
GTIN	4059192002442
Item class	43A

Description

Version:

Clearly legible, high-contrast LCD display. Inductive, waterproof measuring system. The REFERENCE measuring system saves and retains the set zero position, even after being switched on again. The lock function prevents measurement errors arising from accidentally touching the control buttons. The measuring faces are precision-lapped.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

1 battery No. 081560 size CR2032

Technical description

Depth gauge available	yes
Standard	ISO 13385
Depth gauge	rectangular 3.7×1.3
Jaw length	40 mm
Reversible reading	mm / inch
Calibration	A1
Scale divisions	0.01 mm
Scale divisions	0.0005 in

Measuring range	0 - 150 mm
Measured value saving	MAHR reference-lock system
Number of batteries contained	1
Article no of the battery / rechargeable battery fitted	081560 CR2032
IP Index of Protection	IP 67
Power supply	Battery-powered
Measurement deviation E MPE	±0.03 mm
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Universal calipers

Services

DAkkS calibration Calipers / depth gauges maximum measuring range 200 mm	021010 200
Calibration Calipers / depth gauges maximum measuring range 200 mm	021000 200

Accessories

Button cell / special battery Battery type CR2032	081560 CR2032
---	---------------