

Garant GRIDLINE

**Workbench, mobile, left side open, right side cupboard and drawer, height 950mm, Beech marine ply worktop, 20×20G, Worktop length: 1250 mm**



## Order data

Order number	924014 1250
GTIN	4062406101787
Item class	9GG

## Description

### Version:

Workbench in sturdy steel construction with frame of rectangular hollow section. Drawer casing 24G can be locked centrally with cylinder lock. **100% full extension drawers** with differential runners, single-handed individual drawer release system and 75 kg load capacity.

With 2 each ball-bearing fixed wheels and castors, Ø 125 mm, with **treadless polyurethane tyres**, minimum rolling resistance, low noise and fibre shields. Castors with brakes for the wheels and the castor heads.

Casing with door and open casing including height-adjustable galvanized storage shelf.

### Fitted with:

Drawer front height (right) mm: 75

Door height (right) mm: 525

Number of height-adjustable storage shelves (right): 1

### Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts and cupboard doors RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7016 light grey.**

Individual drawer release system: One-hand

Drawer usable area in G: 20×20

Height: 950 mm

Worktop length: 1250 mm

Worktop depth: 750 mm

Worktop thickness: 25 mm

Support cabinet width: 1100 mm

Support cabinet depth: 700 mm

## Technical description

Treadless tyres	yes
Drawer usable width in G	20
Number of fixed wheels without parking brake	2
Number of doors	1
Number of drawers	1
can be lowered	no
Number of castors with parking brake	2
Drawer usable width	500 mm
Drawer usable area in G	20×20
Fixed wheel Ø	125 mm
Worktop thickness	25 mm
ComfortClose	no
Castor Ø	125 mm
Worktop length	1250 mm
Bumper	no
Drawer usable depth in G	20
Weight	100.9 kg
Worktop depth	750 mm
Series	Ready-to-go
Material of worktop	Beech marine ply
Support cabinet width	1100 mm
Drawer body usable height	625 mm
Height	950 mm
Support cabinet depth	700 mm
Drawer usable depth	500 mm
Material of wheel	Polyurethan

Push handle	no
Individual drawer release system	One-hand
Design version	Steel hollow section construction
Material thickness	1 mm
Workbench height	950 mm
Drawer/pull-out shelf load capacity	75 kg
Workbench/desk load capacity - maximum distributed load (on wood)	400 kg
Insert thickness	25 mm
Drawer runner extension (partial/full extension)	100 %
Door opening angle	180 degrees
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20x20G
Type of product	Workbench mobile

## Accessories

Slide handle for GridLine Type KO12	914226 KO12
File set Number of tools 6	952253 6
Screwdriver set Number of tools 10	953521 10
Socket set 1/2 inch Number of tools 32	953821 32
Socket set 1/4 inch and 1/2 inch Number of tools 37	953828 37
Socket set 1/4 inch and 1/2 inch Number of tools 39	953833 39
Pliers set Number of tools 5	954295 5
Pliers set Number of tools 5	954305 5
Hammer set Number of tools 3	954690 3
Marking out and sawing Number of tools 8	954895 8

Lock plate for GridLine Type KO21	914227 KO21
Drawer with one-hand individual drawer release system Drawer front height 75 mm	927805 75
easyPick small parts storage bins set Drawer front height / type 75/1	950300 75/1
easyPick small parts storage bins set Drawer front height / type 75/2	950300 75/2
easyPick small parts storage bins set Drawer front height / type 75/3	950300 75/3
Slotted dividers / plain dividers set Drawer front height / type 75/1	950320 75/1
Slotted dividers / plain dividers set Drawer front height / type 75/2	950320 75/2
Slotted dividers / plain dividers set Drawer front height / type 75/3	950320 75/3
Mat for drawers Dimension in G 20X20	951830 20X20
Non-slip mats set for drawers, 5 pieces Dimension in G 20X20	951885 20X20
Ribbed rubber mat for drawers Dimension in G 20X20	951910 20X20